

绝缘体

陶瓷串珠式、PFA和玻璃纤维套管

单孔圆形(SH)



如欲订购，请访问cn.omega.com/sh_dh_fs_ov，了解价格和详情

绝缘体型号	材质 / 最高温度	适用测温线规格 AWG / Inch	外形尺寸*	
			长度 mm (inch)	外径 mm (inch)
SH-1-8-100	莫来石 1600°C (2910°F)	8 / 0.128	25 (1)	6.0 (¼)
SH-1-14-100		14 / 0.064	25 (1)	4.5 (⅜)
SH-1-20-100		20 / 0.032	25 (1)	3.0 (⅓)
SH-1-24-100		24 / 0.020	25 (1)	1.5 (⅛)

双孔圆形(DH)



绝缘体型号	材质 / 最高温度	适用测温线规格 AWG / Inch	外形尺寸*	
			长度 mm (inch)	外径 mm (inch)
DH-1-8-100	莫来石 1600°C (2910°F)	8 / 0.128	25 (1)	11.1 (7/16)
DH-1-14-100		14 / 0.064	25 (1)	7.0 (9/32)
DH-1-20-100		20 / 0.032	25 (1)	4.0 (5/32)
DH-1-24-100		24 / 0.020	25 (1)	3.0 (⅓)

单孔鱼脊骨形(FS)



材质 / 最高温度	绝缘体型号	适用测温线规格 AWG / Inch	外形尺寸*	
			长度 mm (inch)	外径 mm (inch)
滑石 1200°C (2190°F)	FS-400-8-(†)	8 / 0.128	10.2 (0.40)	10.2 (0.40)
	FS-330-10-(†)	10 / 0.102	8.38 (0.33)	8.38 (0.33)
	FS-260-8-(†)	8 / 0.128	6.60 (0.26)	6.60 (0.26)
	FS-260-12-(†)	12 / 0.081	6.60 (0.26)	6.60 (0.26)
	FS-200-14-(†)	14 / 0.064	5.08 (0.20)	5.08 (0.20)
	FS-170-18-(†)	18 / 0.040	4.32 (0.17)	4.32 (0.17)
	FS-125-20-(†)	20 / 0.032	3.18 (0.13)	3.18 (0.13)
	FS-110-20-(†)	20 / 0.032	2.79 (0.11)	2.79 (0.11)

† 填上数量：500或1000件

双孔椭圆形(OV)




绝缘体型号	材质 / 最高温度	适用测温线规格 AWG / Inch	外形尺寸*		
			长度 mm (inch)	外径 mm (inch)	厚度 mm (inch)
OV-1-8-100	莫来石	8 / 0.128	25 (1)	11.1 (7/16)	6.99 (0.275)
OV-1-14-100	1600°C	14 / 0.064	25 (1)	8.0 (5/16)	5.16 (0.203)
OV-1-20-100	(2910°F)	20 / 0.032	25 (1)	4.4 (1/4)	3.0 (0.118)

* 提供的所有尺寸仅为标称数据。

玻璃纤维套管

玻璃纤维套管适用于不超过480°C (900°F) 应用的裸线的绝缘。



线规 / 颜色	20	24	26	28	30
黑色	FBGS BK 20	FBGS BK 24	FBGS BK 26	FBGS BK 28	FBGS BK 30
黄色	FBGS 有 20	FBGS 有 24	FBGS 有 26	FBGS 有 28	FBGS 有 30
蓝色	FBGS B 20	FBGS B 24	FBGS B 26	FBGS B 28	FBGS B 30
紫色	FBGS P 20	FBGS P 24	FBGS P 26	FBGS P 28	FBGS P 30
红色	FBGS R 20	FBGS R 24	FBGS R 26	FBGS R 28	FBGS R 30
本色	FBGS N 20	FBGS N 24	FBGS N 26	FBGS N 28	FBGS N 30

订购示例：FBGS-BK-20-200，黑色20线规玻璃纤维套管。

PFA管

PFA管适用于温度不超过230°C (450°F)的潮湿或者腐蚀环境应用的测温线的绝缘。



线规 / 颜色	20	24	26	28	30
黑色	TF-BK 20	TF-BK 24	TF-BK 26	TF-BK 28	TF-BK 30
蓝色	TF-B 20	TF-B 24	TF-B 26	TF-B 28	TF-B 30
紫色	TF-P 20	TF-P 24	TF-P 26	TF-P 28	TF-P 30
红色	TF-R 20	TF-R 24	TF-R 26	TF-R 28	TF-R 30
白色	TF-W 20	TF-W 24	TF-W 26	TF-W 28	TF-W 30
黄色	TF-Y 20	TF-Y 24	TF-Y 26	TF-Y 28	TF-Y 30

订购示例：TF-R-20-200，红色20线规PFA管。